

# CULT-IFW

Installation kit flexible wall for CU-LT

K114-B 12/2017

### TABLE OF CONTENTS

CONTENTS • PRODUCT PRESENTATION • LIST OF PARTS • APPLICATION.....2  
MOUNTING .....3

### PRODUCT PRESENTATION

The installation kit flexible wall CULT-IFW facilitates the installation of the damper CU-LT in a flexible wall.

### LIST OF PARTS

Description	Characteristics	Quantity
Board installation kit - for the width	795 x 100	2
Board installation kit - for the height - mechanism side	655 x 100	1
Board installation kit - for the height - non-mechanism side	655 x 100	1
Chipboard screw	Ø5.0 x 30	4
Chipboard screw	Ø5.0 x 60	4
Label 'KIT'	ETIK-D042	1


### APPLICATION




fig. CU-LT




## MOUNTING




1. Cut the boards at the desired length :
  - For the height =  $H + 55\text{mm}$
  - For the width =  $W - 5\text{mm}$
2. Inject the grooves with gypsum




3. Slide the boards over the ribs of the damper.



4. Fasten the 4 corners with chipboard screws of  $\text{Ø}5.0 \times 60$ .



5. Unfold the positioning plates.



6. Fix the positioning plates with chipboard screws of  $\text{Ø}5.0 \times 30$ .

If the product is manipulated in any other way than described in this manual, Rf-Technologies will decline any responsibility and the guarantee will expire!